

YNT56R56R

by Burndy
Catalog ID: YNT56R56R

Prop 65 Notice

Aluminum Compression Two piece T-Tap connector, 230 kV, 1510-1590 kcmil ACSR, 1650 kcmil ACAR, 1700-1800 kcmil Alum., 2 Pad holes



Product Details

General

Connector Type	Tap
Die Index	729
UPC	781810503911
UPC 12 Digit	7818105039111

Dimensions

Dimension - Height inch	11.08 in
Dimension - Length Overall inch	23.65 in

Conductor Related

Conductor - ACAR Str Size	1650 (42/19)
Conductor - ACAR Str Size Range	1650 (42/19)
Conductor - ACSR Str Size	1510.5 (45/7) kcmil;1590 (45/7) kcmil;1590 (54/19) kcmil
Conductor - ACSR Str Size Range	1510.5 (45/7) kcmil -1590 (54/19) kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)