

# YNT594R594RT

by Burndy  
Catalog ID: YNT594R594RT

EXTRUDED COMPRESSION T-TAP RUN & TAP: 2267-250 kcmil ACAR  
2300 kcmil ACSR 2500 kcmil Al



## Product Details

### General

Connector Type	Tap
Die Index	740
Material	Aluminum
UPC	781810180754
UPC 12 Digit	7818101807544

### Dimensions

Dimension - B Length inch	7.6 in
Dimension - Height fraction	11-9/20 in
Dimension - Height inch	11.45 in
Dimension - Length Overall inch	24.3 in
Dimension - Outside Diameter inch	2.6 in

### Conductor Related

Conductor - ACAR Str Run	2267;2500
Conductor - ACAR Str Size	2156 KCMIL - 2167 KCMIL
Conductor - ACAR Str Tap	2267;2500
Conductor - ACSR Str Run	2300
Conductor - ACSR Str Tap	2300 KCMIL
Conductor - AL Str Run	2500 kcmil
Conductor - AL Str Tap	2500 KCMIL

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)