

# YNT59R59R

by Burndy  
Catalog ID: YNT59R59R

Prop 65 Notice

Aluminum Compression T-Tap connector, 230 kV, 2156-2167 kcmil ACSR, 2300 kcmil Aluminum, 2 Pad holes



## Product Details

### General

Connector Type	Tap
Die Index	735
Material	Aluminum
UPC	781810343425
UPC 12 Digit	7818103434255

### Dimensions

Dimension - B Length inch	6.82 in
Dimension - Height inch	10.86 in
Dimension - Length Overall inch	23.21 in

### Conductor Related

Conductor - ACSR Str Size	2156 (84/19) kcmil;2167 (72/7) kcmil
Conductor - ACSR Str Size Range	2156 (84/19) kcmil -2167 (72/7) kcmil
Conductor - AL Str Size	2300 kcmil
Conductor - AL Str Size Range	2300 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)