

YNTA32R

by Burndy
Catalog ID: YNTA32R

Prop 65 Notice

Terminal Tee Pads,ACAR: 300 KCMIL - 336.4 KCMIL ALUMINUM: 336.4 KCMIL - 350 KCMIL DIE INDEX: 717, 1.75" Spacing



Product Details

General

Connector Type	Tap
Die Index	717
Material	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Pad Configuration	2 Hole NEMA
Plated	N
Prefilled Oxide Inhibitor	N
UPC	781810016534
UPC 12 Digit	7818100165344

Dimensions

Dimension - B Length inch	3.9 in
Dimension - Bolt Size fraction	1/2 in
Dimension - Bolt Size inch	0.5 in
Dimension - D inch	3.12 in
Dimension - Height fraction	4-47/50 in
Dimension - Height inch	4.94 in
Dimension - Length Overall inch	15.46 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	2.00 in

Conductor Related

Conductor - ACAR Str Size	300 KCMIL - 336.4 KCMIL
Conductor - ACAR Str Size Range	300 KCMIL - 336.4 KCMIL
Conductor - ACSR Str Size	300 KCMIL - 336.4 KCMIL
Conductor - ACSR Str Size Range	336.4 (26/7) Kcmil-336.4 (30/7) Kcmil
Conductor - AL Str Size	336.4;350
Conductor - AL Str Size Range	336.4-350

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)