

YNTA36R

by Burndy
Catalog ID: YNTA36R

Prop 65 Notice

Terminal Tee Taps,WIRE: 477 kcmil ACSR 500-556.5 kcmil ALUM. INDEX: 720, 1.75" Spacing



Product Details

General

Connector Type	Tap
Die Index	720
Material	Aluminum
UPC	781810053652
UPC 12 Digit	7818100536522

Dimensions

Dimension - B Length inch	4.19 in
Dimension - Bolt Size fraction	1/2 in
Dimension - Bolt Size inch	0.5 in
Dimension - D inch	3.12 in
Dimension - Height fraction	5-4/25 in
Dimension - Height inch	5.16 in
Dimension - Length Overall inch	16.29 in
Dimension - Outside Diameter inch	1.41 in
Dimension - Pad Width inch	2.25 in

Conductor Related

Conductor - ACAR Str Size	477 KCMIL
Conductor - ACAR Str Size Range	500 KCMIL - 556.5 KCMIL
Conductor - ACSR Str Size	477.0 (24/7) Kcmil;477.0 (26/7) Kcmil
Conductor - ACSR Str Size Range	477.0 (24/7) Kcmil-477.0 (26/7) Kcmil
Conductor - AL Str Size	500;550;556.5
Conductor - AL Str Size Range	500-556.5

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)