

YNTA39RHT

by Burndy
Catalog ID: YNTA39RHT

T-Tap with Pad for ACSS Conductor



Product Details

General

Connector Type	Tap
Physical Attribute - Number of Holes	4
UPC	781810515204
UPC 12 Digit	7818105152044

Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.13 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height inch	5.25 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	25.64
Dimension - Pad Width inch	3.25 in

Conductor Related

Conductor - ACSS Str Size	556.5 (24/7) kcmil;556.5 (26/7) kcmil
---------------------------	---------------------------------------

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)