

YNTA54R

by Burndy
Catalog ID: YNTA54R

Prop 65 Notice

T-TAP WITH PAD TAP.



Product Details

General

Connector Type	Tap
Die Index	728
Material	Aluminum
UPC	781810038352
UPC 12 Digit	7818100383522

Dimensions

Dimension - B Length inch	6 in
Dimension - Height fraction	6 in
Dimension - Height inch	6.00 in
Dimension - L Length Overall mm	541 mm
Dimension - Length Overall inch	21.61 in
Dimension - Outside Diameter inch	2.25 in
Dimension - Pad Width inch	3.25 in
Thickness - Pad	0.69 in

Conductor Related

Conductor - ACSR Str Size	1113 (54/19) Kcmil;1192.5 (45/7) Kcmil;1272 (45/7) Kcmil;1272 (54/19) Kcmil;1351.5 (45/7) Kcmil;1351.5 (54/19) Kcmil
Conductor - ACSR Str Size Range	1113 (54/19) Kcmil-1351.5 (54/19) Kcmil
Conductor - AL Str Size	1351.5;1400;1431.0;1500;1590;1600
Conductor - AL Str Size Range	1351.5-1600

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)