

YNTA56R

by Burndy
Catalog ID: YNTA56R

Prop 65 Notice

T-TAP WITH PAD TAP.



Product Details

General

Connector Type	Tap
Die Index	729
Material	Aluminum
UPC	781810180815
UPC 12 Digit	7818101808155

Dimensions

Dimension - B Length inch	6.94 in
Dimension - Height fraction	6-1/4 in
Dimension - Height inch	6.25 in
Dimension - L Length Overall mm	601 mm
Dimension - Length Overall inch	23.65 in
Dimension - Outside Diameter inch	2.5 in
Dimension - Pad Width inch	3.59 in
Thickness - Pad	0.69 in

Conductor Related

Conductor - ACAR Str Size	1650 Kcmil
Conductor - ACSR Str Size	1510.5 (45/7) kcmil;1510.5 (54/19) Kcmil;1590 (45/7) Kcmil;1590 (54/19) Kcmil
Conductor - ACSR Str Size Range	1510.5 (45/7) kcmil-1590 (54/19) Kcmil
Conductor - AL Str Size	1700 Kcmil;1800 Kcmil
Conductor - AL Str Size Range	1700 Kcmil - 1800 Kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)