

YNTA58R

by Burndy
Catalog ID: YNTA58R

Prop 65 Notice

T-TAP WITH PAD TAP.



Product Details

General

| | |
|----------------|---------------|
| Connector Type | Tap |
| Die Index | 735 |
| Material | Aluminum |
| UPC | 781810180839 |
| UPC 12 Digit | 7818101808399 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length inch | 6.91 in |
| Dimension - Height fraction | 6-1/4 in |
| Dimension - Height inch | 6.25 in |
| Dimension - L Length Overall mm | 598 mm |
| Dimension - Length Overall inch | 23.53 in |
| Dimension - Outside Diameter inch | 2.5 in |
| Dimension - Pad Width inch | 3.59 in |
| Thickness - Pad | 0.69 in |

Conductor Related

| | |
|---------------------------|--------------------|
| Conductor - ACSR Str Size | 1780 (84/19) kcmil |
| Conductor - AL Str Size | 2000 kcmil |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)