

YNTA594RKIT

by Burndy
Catalog ID: YNTA594RKIT



Product Details

General

Connector Type	Tap
Die Index	740
Material	Aluminum
UPC	781810486085
UPC 12 Digit	7818104860855

Dimensions

Dimension - B Length inch	7.6 in
Dimension - Height fraction	10-7/10 in
Dimension - Height inch	10.7 in
Dimension - L Length Overall mm	617 mm
Dimension - Length Overall inch	24.3 in
Dimension - Outside Diameter inch	1.25 in
Thickness - Pad	0.86 in

Conductor Related

Conductor - ACAR Str Size	2267 Kcmil; 2500 Kcmil
Conductor - ACAR Str Size Range	2267-2500 Kcmil
Conductor - ACSR Str Size	2300 Kcmil
Conductor - AL Str Size	2500 Kcmil

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)