

YNU32R

by Burndy
Catalog ID: YNU32R

Prop 65 Notice

Al Repair sleeve, HV and EHV applications, 300-336.4 Kcmil ACSR, 14 IN L, 717 Index, For temporary restoration of conductivity to damaged ACSR Trnsmnsn. Lines



Product Details

General

| | |
|----------------|---------------|
| Connector Type | Splice |
| Die Index | 717 |
| Material | Aluminum |
| UPC | 781810180860 |
| UPC 12 Digit | 7818101808600 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - L Length Overall mm | 356 mm |
| Dimension - Length Overall inch | 14.00 in |
| Dimension - Outside Diameter inch | 1.19 in |

Conductor Related

| | |
|---------------------------------|-------------------------|
| Conductor - ACSR Str Size Range | 300 Kcmil - 336.4 Kcmil |
| Conductor - AL Str Size Range | 336.4 Kcmil - 350 Kcmil |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)