

YNU451RHT

by Burndy
Catalog ID: YNU451RHT

Prop 65 Notice

Repair Sleeve for ACSS Conductor



Product Details

General

Connector Type	Splice
Die Index	725
UPC	781810491539
UPC 12 Digit	7818104915399

Dimensions

Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24.00 in

Conductor Related

Conductor - ACSS Str Size	715.5 (26/7) kcmil;795 (24/7) kcmil;795 (26/7) kcmil;795 (45/7) kcmil;795 (54/7) kcmil
Conductor - ACSS Str Size Range	715.5 (26/7) kcmil-795 (54/7) kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)