

YNU451R

by Burndy
Catalog ID: YNU451R

Prop 65 Notice

Al Repair Sleeve, 715.5 - 874.5 kcmil ACSR, 795 - 1000 kcmil Al, 16.00" L, 725 Index



Product Details

General

Connector Type	Splice
Die Index	725
Material	Aluminum
Prefilled Oxide Inhibitor	Y
UPC	781810016558
UPC 12 Digit	7818100165588

Dimensions

Dimension - L Length Overall mm	406 mm
Dimension - Length Overall inch	16.00 in
Dimension - Outside Diameter inch	1.8 in

Conductor Related

Conductor - ACSR Str Size Range	715.5 Kcmil - 874.5 Kcmil
Conductor - AL Str Size Range	795 Kcmil - 1000 Kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)