

# YNU49RHT

by Burndy  
Catalog ID: YNU49RHT

Repair Sleeve for ACSS Conductor



## Product Details

### General

Connector Type	Splice
Die Index	727
UPC	781810515303
UPC 12 Digit	7818105153033

### Dimensions

Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24.00 in

### Conductor Related

Conductor - ACSS Str Size	900 (45/7) kcmil;900 (54/7) kcmil;954 (42/7) kcmil;954 (20/7) kcmil;954 (45/7) kcmil;954 (48/7) kcmil;954 (24/7) kcmil;954 (54/7) kcmil;954 (30/19) kcmil;1033.5 (42/7) kcmil;1033.5 (45/7) kcmil;1033.5 (48/7) kcmil;1033.5 (54/7) kcmil;1113 (42/7) kcmil;1113 (45/7) kcmil
Conductor - ACSS Str Size Range	900 (45/7) kcmil-1113 (45/7) kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

### Logistics

Minimum Pack Quantity	6
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)