

YNU49R

by Burndy
Catalog ID: YNU49R

Prop 65 Notice

Al Repair sleeve, HV and EHV applications, 900 - 1113 Kcmil ACSR, 16 IN L, 727 Index, For temporary restoration of conductivity to damaged ACSR Transmission Lines



Product Details

General

Connector Type	Splice
Die Index	727
Material	Aluminum
UPC	781810000564
UPC 12 Digit	7818100005644

Dimensions

Dimension - L Length Overall mm	406 mm
Dimension - Length Overall inch	16.00 in
Dimension - Outside Diameter inch	1.97 in

Conductor Related

Conductor - ACSR Str Size	900 (45/7) Kcmil;954 (45/7) Kcmil;954 (54/7) Kcmil;1033.5 (45/7) Kcmil;1033.5 (54/7) Kcmil;1113 (45/7) Kcmil
Conductor - ACSR Str Size Range	900 (45/7) Kcmil-1113 (45/7) Kcmil
Conductor - AL Str Size Range	1033.5 Kcmil - 1272 Kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)