

# YNU56R

by Burndy  
Catalog ID: YNU56R

Prop 65 Notice

Al Repair sleeve, HV and EHV applications, 1510.5 - 1590 Kcmil ACSR, 19 IN L, 729 Index, For temporary restoration of conductivity to damaged ACSR Transmission Lines



## Product Details

### General

Connector Type	Splice
Die Index	729
Material	Aluminum
UPC	781810129357
UPC 12 Digit	7818101293577

### Dimensions

Dimension - L Length Overall mm	483 mm
Dimension - Length Overall inch	19.00 in
Dimension - Outside Diameter inch	2.5 in

### Conductor Related

Conductor - ACSR Str Size	1510.5 (45/7) kcmil;1510.5 (54/19) Kcmil;1590 (45/7) kcmil;1590 (54/19) kcmil
Conductor - ACSR Str Size Range	1510.5 (45/7) kcmil-1590 (54/19) kcmil
Conductor - AL Str Size	1700 kcmil;1750 kcmil;1800 kcmil
Conductor - AL Str Size Range	1700 kcmil-1800 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)