

YNU59RHT

by Burndy
Catalog ID: YNU59RHT

Prop 65 Notice

Repair Sleeve for ACSS Conductor



Product Details

General

Connector Type	Splice
Die Index	735
UPC	621945468696
UPC 12 Digit	781810515358

Dimensions

Dimension - L Length Overall mm	686 mm
Dimension - Length Overall inch	27.00 in

Conductor Related

Conductor - ACSS Str Size	2156 (84/19) kcmil;2167 (72/7) kcmil
Conductor - ACSS Str Size Range	2156 (84/19) kcmil-2167 (72/7) kcmil

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Logistics

Minimum Pack Quantity	8
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)