

YOT361R361R

by Burndy
Catalog ID: YOT361R361R

Prop 65 Notice

Aluminum T-Tap Connector, 426 or M index, 477 (18-1) ACSR 477 (19, 37) AAC



Product Details

General

Connector Type	Tap
Die Index Run Side	426;M
Die Index Tap Side	426;M
Material	Aluminum Alloy
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
UPC	781810016107

Dimensions

Dimension - Height fraction	6-1/4 in
Dimension - Height inch	6.25 in
Dimension - L Length Overall mm	314 mm
Dimension - Length Overall inch	12.375 in

Conductor Related

Conductor - AAAC 5005 Run	30.58 (7) kcmil
Conductor - AAAC 5005 Run Range	30.58 (7) kcmil
Conductor - AAAC 5005 Tap	30.58 (7) kcmil
Conductor - AAAC 5005 Tap Range	30.58 (7) kcmil
Conductor - AAAC 6201 Run	30.58 (7) kcmil
Conductor - AAAC 6201 Run Range	30.58 (7) kcmil
Conductor - AAAC 6201 Tap	30.58 (7) kcmil
Conductor - AAAC 6201 Tap Range	30.58 (7) kcmil
Conductor - ACSR Str Run	477.0 (18/1) Pelican kcmil
Conductor - ACSR Str Run Range	477.0 (18/1) Pelican kcmil
Conductor - ACSR Str Tap	477.0 (18/1) Pelican kcmil
Conductor - ACSR Str Tap Range	477.0 (18/1) Pelican kcmil
Conductor - AL Str Run	477 kcmil
Conductor - AL Str Run Range	477 kcmil
Conductor - AL Str Tap	477 kcmil

Conductor - AL Str Tap Range	477 kcmil
------------------------------	-----------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	6
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)