


YP29C261

by Burndy
Catalog ID: YP29C261

Prop 65 Notice

Figure 6 - shaped, wide range-taking CU compression tap connector for primary service taps and secondary service drops.

Features: Compression Tap Connector For Primary Service Taps And Secondary Service Drops, Connector Can Be Gripped In Tool And Slipped Over The Line For Easy Installation, Conductor Type: Run And Tap: Copper



Product Details

General

Application	Line Tap for Extra Wide Range of Copper
Connector Type	Tap
Material	Copper
Plated	Y
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	Overhead Bare Connectors
UPC	781810461822
UPC 12 Digit	7818104618222

Dimensions

Dimension - Height inch	2.00 in
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	1.00 in

Conductor Related

Conductor - Copper Str Run	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Run Range	1/0 AWG-250 kcmil
Conductor - Copper Str Tap	4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Tap Range	4 AWG-2/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)