

YPC28U26

by Burndy
Catalog ID: YPC28U26



Figure 6 shape connector separates run and tap wires and minimizes galvanic corrosion of conductors, Run ACSR, 5005:1/0-4/0.

Features: Extra Wide Range Universal Connector, Two Dies And 5 Connectors Take Run Sizes 1/0- 600 KCMIL, And Tap Sizes 6-400 KCMIL, Wide Range Made Possible By Long Ram Travel Of BURNDY HYPRESS Tools, Figure 6- Shape Separates Run And Tap Wires, And Minimizes Galvanic Corrosion Of Conductors, Connector Can Be Gripped In Tool And Slipped Over Line For Easy Installation, Pre-Filled With PENETROX Joint Compound And Stripsealed, Conductor Type: ACSR, 5005, Aluminum And Copper, Shape: 6, Die Index: D3 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U-D3 Die, (2), Y45 Tool, U-D3 Die With PT-6515 Adapter, (2), Y46 Tool, U-D3 Die With PUADP-1 Adapter, (2)

Product Details

General

Application	For Combinations Of Copper, Aluminum, ACSR, 6201, 5005 And Compressed And Compact Conductors
Die Index	D3
Material	Aluminum
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YPC-U
UPC	781810136508
UPC 12 Digit	7818101365088

Dimensions

Dimension - Height inch	2.06 in
Dimension - L Length Overall mm	54 mm
Dimension - Length Overall inch	2.12 in

Conductor Related

Conductor - ACSR Str Run	1/0 AWG, 2/0 AWG, 3/0 AWG, 4/0 AWG
Conductor - ACSR Str Run Range	1/0 AWG-4/0 AWG
Conductor - ACSR Str Tap	6 AWG, 1/0 AWG
Conductor - ACSR Str Tap Range	6 AWG-1/0 AWG
Conductor - AL Str Run	1/0 AWG; 2/0 AWG; 3/0 AWG; 4/0 AWG
Conductor - AL Str Run Range	1/0 AWG-4/0 AWG
Conductor - AL Str Tap	3 AWG; 2 AWG; 1 AWG; 1/0 AWG; 2/0 AWG
Conductor - AL Str Tap Range	3 AWG-2/0 AWG
Conductor - Copper Str Run	1/0 AWG, 2/0 AWG, 3/0 AWG, 4/0 AWG
Conductor - Copper Str Run Range	1/0 AWG, 2/0 AWG, 3/0 AWG, 4/0 AWG

Conductor - Copper Str Tap	6 AWG, 2/0 AWG
Conductor - Copper Str Tap Range	6 AWG-2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • CU C Solid-Run • ACSR C Str-Run • AL C Str-Tap • CU C Str-Tap • CU C Solid-Tap • ACSR C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)