

YPC33R33R

by Burndy
Catalog ID: YPC33R33R



Figure 6 shape connector separates run and tap wires and minimizes galvanic corrosion of conductors, Run ACSR, 5005:266.8 (18-1) - 397.5 (18-1).

Features: Extra Wide Range Universal Connector, Two Dies And 5 Connectors Take Run Sizes 1/0- 600 KCMIL, And Tap Sizes 6-400 KCMIL, Wide Range Made Possible By Long Ram Travel Of BURNDY HYPRESS Tools, Figure 6- Shape Separates Run And Tap Wires, And Minimizes Galvanic Corrosion Of Conductors, Connector Can Be Gripped In Tool And Slipped Over Line For Easy Installation, Pre-Filled With PENETROX Joint Compound And Stripsealed, Conductor Type: ACSR, 5005, Aluminum And Copper, Shape: 6, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U-N Die, (3), Y45 Tool, S-N Die, (3), Y46 Tool, P-N Die, (3), Die Index: N Element A

Product Details

General

Application	For Combinations Of Copper, Aluminum, ACSR, 6201, 5005 And Compressed And Compact Conductors
Die Index	N
Material	Aluminum
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YPC-U
UPC	781810138205
UPC 12 Digit	7818101382055

Dimensions

Dimension - Height inch	2.28 in
Dimension - L Length Overall mm	98 mm
Dimension - Length Overall inch	3.88 in
Dimension - Width inch	1.23 in

Conductor Related

Conductor - ACSR Str Run Range	266.8 kcmil-397.5 kcmil
Conductor - ACSR Str Tap Range	266.8 kcmil-397.5 kcmil
Conductor - AL Str Run	250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil
Conductor - AL Str Run Range	250 kcmil-400 kcmil
Conductor - AL Str Tap	250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil
Conductor - AL Str Tap Range	250 kcmil-400 kcmil
Conductor - Copper Str Run	250 kcmil;300 kcmil;350 kcmil;400 kcmil
Conductor - Copper Str Run Range	250 kcmil-400 kcmil
Conductor - Copper Str Tap	250 kcmil;300 kcmil;350 kcmil;400 kcmil

Conductor - Copper Str Tap Range	250 kcmil-400 kcmil
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • CU C Solid-Run • ACSR C Str-Run • AL C Str-Tap • CU C Str-Tap • CU C Solid-Tap • ACSR C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)