

YQE91

by Burndy
Catalog ID: YQE91

Brass Pigtail Splice, 14-18 AWG, 600 V, 0.76" L, Nylon Insul, Tin Plated, 1000V(for building wiring).

Features: Rated At 600 Volts For Building Wire And 1000 Volts For Fixtures And Signs, The BURCAP Is Designed To Splice A Wide Range Of Different Cable Sizes, Installation Tool: M8ND, Y8ND Tool With N150WT Die, Wire Strip Length: 5/16 IN



Product Details

General

Application	For Splicing A Wide Range Of Different Cable Sizes
Connector Type	Splice
Insulation	Y
Insulation Type	Nylon
Material	Copper
Plated	N
Plating Type	Tin
Sub Brand	INSULINK
Trade Name	INSULINK™
Type	YQE
UPC	781810029480
UPC 12 Digit	7818100294800

Dimensions

Dimension - B Length fraction	3/10 in
Dimension - B Length inch	0.30 in
Dimension - L Length Overall mm	19 mm
Dimension - Length Overall inch	0.76 in
Dimension - Pad Width inch	0.24 in
Dimension - Strip Length inch	5/16

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Solid Size	18 AWG;17 AWG;16 AWG;15 AWG;14 AWG
-------------------------------	------------------------------------

Conductor - Copper Solid Size Range	18 AWG-14 AWG
Conductor - Copper Str Size	18 AWG;16 AWG;14 AWG
Conductor - Copper Str Size Range	18 AWG-14 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)