

YRA1CU1

by Burndy
Catalog ID: YRA1CU1

Prop 65 Notice

AL compression lug for joining AL and CU cable to transformer and equipment pads, Prefilled with PENETROX, Outside Dia: .56 IN



Product Details

General

Die Index	243;BG
Material	Aluminum
Physical Attribute - Pad Configuration	1 Hole
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810016886
UPC 12 Digit	7818100168866

Dimensions

Dimension - B Length fraction	2-9/16 in
Dimension - B Length inch	0.960 in
Dimension - D inch	1.19 in
Dimension - L Length Overall mm	67 mm
Dimension - Length Overall inch	2.62 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.64 in
Dimension - Strip Length inch	1 in
Physical Attribute - Tongue Angle	Straight
Thickness - Pad	0.29 in

Conductor Related

Conductor - ACSR Str Size	2 AWG
Conductor - AL Str Size	1 AWG, 2 AWG
Conductor - AL Str Size Range	1 AWG-2 AWG
Conductor - Copper Str Size	1 AWG, 2 AWG, 3 AWG
Conductor - Copper Str Size Range	1 AWG-3 AWG

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)