

YRA26UTN

by Burndy
Catalog ID: YRA26UTN

Al Compression Terminal, 1 Hole, 2/0 AWG ACSR, 2/0 Str Al/Cu, 0.56" Hole Dia., Tin Plated



Product Details

General

Material	Aluminum
Plated	Y
Plating Type	Tin - Electro Plated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810085141
UPC 12 Digit	7818100851411

Dimensions

Dimension - B Length inch	1.43 in
Dimension - D inch	1.28 in
Dimension - L Length Overall mm	81 mm
Dimension - Length Overall inch	3.19 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.91 in
Dimension - Pad Width inch	0.91 in
Dimension - Strip Length inch	1 1/2 in
Thickness - Pad	0.25 in

Conductor Related

Conductor - ACSR Str Size	2/0 AWG
Conductor - AL Str Size	2/0 AWG
Conductor - Copper Str Size	2/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)