

YRB2525TW

by Burndy
Catalog ID: YRB2525TW

Prop 65 Notice

Cu Splice, 1/0(Cu)(Barrel A & B), 35 kV, 2.63" L, Hot Tin Dipped Plating, Pink, 12 or 348 Index, For Cu to Cu



Product Details

General

Color Code	Pink
Die Index	12;348
Material	Copper
Plating Type	Tin - Hot Dipped
Trade Name	HYREDUCER™
UPC	781810192825
UPC 12 Digit	7818101928255

Dimensions

Dimension - B Length inch	0.98 in
Dimension - Length Overall inch	2.63 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Strip Length inch	1-1/16 in

Conductor Related

Conductor - Copper Str Size A	1/0 AWG
Conductor - Copper Str Size B	1/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)