

YRB252CTTN

by Burndy
Catalog ID: YRB252CTTN

Prop 65 Notice

Copper HYREDUCER™; 2.63 in L; Tin Plated; 1/0 AWG (Barrel A); #2 AWG (STR) (Barrel B)



Product Details

General

Color Code	Pink
Die Index	12;348
Material	Copper
Plating Type	Tin
Trade Name	HYREDUCER™
UPC	781810439296
UPC 12 Digit	7818104392966

Dimensions

Dimension - B Length inch	0.98 in
Dimension - Length Overall inch	2.63 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Strip Length inch	1-1/16 in

Conductor Related

Conductor - Copper Str Size A	1/0 AWG
Conductor - Copper Str Size B	#2 AWG (STR)

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)