

YRB25U2TTN

by Burndy
Catalog ID: YRB25U2TTN

Aluminium HYREDUCER™; 3.25 in L; Tin Plated; 1/0 (19 STR) AWG (Barrel A); #2 (7 STR) AWG (Barrel B)



Product Details

General

Color Code	Orange; Tan
Connector Type	Reducer
Die Index	14;296
Material	Aluminum
Plating Type	Tin
Trade Name	HYREDUCER™
UPC	781810246818
UPC 12 Digit	7818102468188

Dimensions

Dimension - B Length inch	1.35 in
Dimension - Length Overall inch	3.25 in
Dimension - Outside Diameter inch	0.65 in
Dimension - Strip Length inch	1-7/16 in

Conductor Related

Conductor - AL Str Size A	1/0 (19 STR) AWG
Conductor - AL Str Size B	#2 (7 STR) AWG
Conductor - Copper Str Size A	1/0 (19 STR) AWG
Conductor - Copper Str Size B	#2 (7 STR) AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)