

# YRB27U25TW

by Burndy  
Catalog ID: YRB27U25TW

Prop 65 Notice

Al HYREDUCER™ Splice, 3.69" L, 3/0 (19 STR) AWG (Al/Cu)(Barrel A), 1/0 (19 STR) AWG (Al/Cu)(Barrel B), White, 298 Index, For Al to Al&Al to Cu



## Product Details

### General

Color Code	White
Connector Type	Reducer
Die Index	298
Material	Aluminum
Plating Type	Tin - Hot Dipped
Trade Name	HYREDUCER™
UPC	781810209059
UPC 12 Digit	7818102090599

### Dimensions

Dimension - B Length inch	1.53 in
Dimension - Length Overall inch	3.69 in
Dimension - Outside Diameter inch	0.85 in
Dimension - Strip Length inch	1-5/8 in

### Conductor Related

Conductor - AL Str Size A	3/0 (19 STR) AWG
Conductor - AL Str Size B	1/0 (19 STR) AWG
Conductor - Copper Str Size A	3/0 (19 STR) AWG
Conductor - Copper Str Size B	1/0 (19 STR) AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)