

YRB2828T

by Burndy
Catalog ID: YRB2828T

Prop 65 Notice

Copper HYREDUCER™; 2.84 in L; Hot Tin Dipped; 4/0 (.528) (Barrel A);
4/0 (.528) (Barrel B)



Product Details

General

Color Code	Purple
Die Index	15
Material	Copper
Trade Name	HYREDUCER™
UPC	781810367827
UPC 12 Digit	7818103678277

Dimensions

Dimension - B Length inch	1.16 in
Dimension - Length Overall inch	2.84 in
Dimension - Outside Diameter inch	0.69 in
Dimension - Strip Length inch	1-7/32 in

Conductor Related

Conductor - Copper Str Size A	4/0 AWG
Conductor - Copper Str Size B	4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)