

YRB28U25

by Burndy
Catalog ID: YRB28U25

Prop 65 Notice

Aluminum Electro tin plated reducer; UL Listed; Rating KVA 35 KV



Product Details

General

Color Code	White
Connector Type	Reducer
Die Index	298
Feature - Barrel Style	Chamfered
Material	Aluminum
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYREDUCER™
UPC	781810176795
UPC 12 Digit	7818101767955

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.36 in
Dimension - L Length Overall mm	84 mm
Dimension - Length Overall inch	3.31 in
Dimension - Outside Diameter inch	0.85 in
Dimension - Strip Length inch	1-7/16

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - AL Str Size A	4/0
Conductor - AL Str Size A Range	4/0
Conductor - AL Str Size B	1/0
Conductor - AL Str Size B Range	1/0
Conductor - Copper Str Size	4/0
Conductor - Copper Str Size B	1/0

Conductor - Copper Str Size B Range	1/0
-------------------------------------	-----

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)