

YRB28U26TW

by Burndy
Catalog ID: YRB28U26TW

Prop 65 Notice

Al HYREDUCER™ Splice, 3.69" L, 4/0 (19 STR) AWG (Al/Cu)(Barrel A), 2/0 (19 STR) AWG (Al/Cu)(Barrel B), White, 298 Index, For Al to Al&Al to Cu



Product Details

General

Color Code	White
Connector Type	Reducer
Die Index	298
Material	Aluminum
Plating Type	Tin - Hot Dipped
Trade Name	HYREDUCER™
UPC	781810209080
UPC 12 Digit	7818102090800

Dimensions

Dimension - B Length inch	1.53 in
Dimension - Length Overall inch	3.69 in
Dimension - Outside Diameter inch	0.85 in
Dimension - Strip Length inch	1-5/8 in

Conductor Related

Conductor - AL Str Size A	4/0 (19 STR) AWG
Conductor - AL Str Size B	2/0 (19 STR) AWG
Conductor - Copper Str Size A	4/0 (19 STR) AWG
Conductor - Copper Str Size B	2/0 (19 STR) AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)