

YRB29U28

by Burndy
Catalog ID: YRB29U28

Prop 65 Notice

Aluminum Electro tin plated reducer; UL Listed; Rating KVA 35 KV



Product Details

General

Color Code	Brown
Connector Type	Reducer
Die Index	299
Feature - Barrel Style	Chamfered
Material	Aluminum
Physical Attribute - Number of Crimps Required	2
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYREDUCER™
UPC	781810084878
UPC 12 Digit	7818100848788

Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.73 in
Dimension - L Length Overall mm	107 mm
Dimension - Length Overall inch	4.21 in
Dimension - Outside Diameter inch	1.11 in
Dimension - Strip Length inch	1-13/16

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - AL Str Size A	250 kcmil
Conductor - AL Str Size A Range	250 kcmil
Conductor - AL Str Size B	4/0 AWG
Conductor - AL Str Size B Range	4/0 AWG
Conductor - Copper Str Size	250

Conductor - Copper Str Size A	250 kcmil
Conductor - Copper Str Size A Range	250 kcmil
Conductor - Copper Str Size B	4/0 AWG
Conductor - Copper Str Size B Range	4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)