

YRB30U28

by Burndy
Catalog ID: YRB30U28

Aluminum Electro tin plated reducer



Product Details

General

| | |
|------------------------|----------------------|
| Color Code | Brown |
| Connector Type | Reducer |
| Die Index | 299 |
| Feature - Barrel Style | Chamfered |
| Material | Aluminum |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Temperature Rating | 194 |
| Trade Name | HYREDUCER™ |
| UPC | 781810739556 |
| UPC 12 Digit | 7818107395566 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length fraction | 1-3/4 in |
| Dimension - B Length inch | 1.73 in |
| Dimension - L Length Overall mm | 107 mm |
| Dimension - Length Overall inch | 4.21 in |
| Dimension - Outside Diameter inch | 1.11 in |
| Dimension - Strip Length inch | 1-13/16 |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|---------------------------------|---------|
| Conductor - AL Str Size A | 350 AWG |
| Conductor - AL Str Size A Range | 350 AWG |
| Conductor - AL Str Size B | 4/0 |
| Conductor - AL Str Size B Range | 4/0 |
| Conductor - Copper Str Size | 350 AWG |
| Conductor - Copper Str Size B | 4/0 |

| | |
|-------------------------------------|-----|
| Conductor - Copper Str Size B Range | 4/0 |
|-------------------------------------|-----|

Certifications and Compliance

| | |
|------------------------------------|--------------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 25 |
|-----------------------|----|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)