

YRB3228TTN

by Burndy
Catalog ID: YRB3228TTN

Prop 65 Notice

HYREDUCER™, Tin plated, 3.48 in long



Product Details

General

Color Code	Blue
Die Index	19;470
Material	Copper
Plated	Y
Plating Type	Tin Plated
Trade Name	HYREDUCER™
UPC	781810308288

Dimensions

Dimension - B Length inch	1.38 in
Dimension - Length BB inch	1.38 in
Dimension - Length Overall inch	3.48 in
Dimension - Outside Diameter inch	0.95 in

Conductor Related

Conductor - Copper Str Size A	400 kcmil
Conductor - Copper Str Size B	4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)