

# YRB32U30

by Burndy  
Catalog ID: YRB32U30

Aluminum Electro tin plated reducer



## Product Details

### General

Color Code	Pink
Connector Type	Reducer
Die Index	300
Material	Aluminum
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYREDUCER™
UPC	781810739839
UPC 12 Digit	7818107398399

### Dimensions

Dimension - B Length fraction	2-1/8 in
Dimension - B Length inch	2.11 in
Dimension - L Length Overall mm	130 mm
Dimension - Length Overall inch	5.12 in
Dimension - Outside Diameter inch	1.31 in
Dimension - Strip Length inch	2-3/16

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - AL Str Size A	400
Conductor - AL Str Size A Range	400
Conductor - AL Str Size B	300
Conductor - AL Str Size B Range	300
Conductor - Copper Str Size	400
Conductor - Copper Str Size B	300

Conductor - Copper Str Size B Range	300
-------------------------------------	-----

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	20
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)