

YRB3431TTN

by Burndy
Catalog ID: YRB3431TTN

Prop 65 Notice

HYREDUCER™, Tin plated, 500-350 kcmil, 4.50 in long



Product Details

General

Accessory Type	Perimeter Half Sub Plate Bracket
Application	10" Fire-Rated Poke-Through Series
Application - For Use On	Concrete
Color Code	Brown
Die Index	20;299
Finish Type	White Paint
Item Type	10" Recessed Fire-Rated Poke-Through Components
Material	Galvanized Steel Copper
Material - Mounting Hardware	Mounting Hardware Included
Plated	Y
Plating Type	Tin Plated
Style	Sub-Plates
Trade Name	HYREDUCER™
UPC	783585548166 781810439517

Dimensions

Dimension - B Length inch	1.73 in
Dimension - Length BB inch	1.73 in
Dimension - Length Overall inch	4.50 in
Dimension - Outside Diameter inch	1.06 in

Conductor Related

Conductor - Copper Str Size A	500 kcmil
Conductor - Copper Str Size B	350 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	cULus Listed
Standards - RoHS Compliance Status	EX

UL Listed	No
-----------	----

Logistics

Carton Quantity	50 EA
-----------------	-------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)