

YRB34U30TW

by Burndy
Catalog ID: YRB34U30TW

Prop 65 Notice

HYREDUCER™-500/300, Hot tin dipped, 6.00" long



Product Details

General

Color Code	Pink
Connector Type	Reducer
Die Index	300
Material	Aluminum
Plating Type	Tin - Hot Dipped
Trade Name	HYREDUCER™
UPC	781810209141

Dimensions

Dimension - B Length fraction	2-7/10 in
Dimension - B Length inch	2.70 in
Dimension - Length Overall inch	6.00 in
Dimension - Outside Diameter inch	1.31 in
Dimension - Strip Length inch	2-13/16 in

Conductor Related

Conductor - AL Str Size A	500 kcmil
Conductor - AL Str Size B	300 kcmil
Conductor - Copper Str Size A	500 kcmil
Conductor - Copper Str Size B	300 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)