

# YRB34U31TW

by Burndy  
Catalog ID: YRB34U31TW

Prop 65 Notice

Al Hyreducer Splice, 6.00" L, 500 kcmil(Al/Cu)(Barrel A), 350 kcmil(Al/Cu)(Barrel B), Hot Tin Dipped Plating, Pink, 300 Index, For Al to Al&Al to Cu



## Product Details

### General

|                |                  |
|----------------|------------------|
| Color Code     | Pink             |
| Connector Type | Reducer          |
| Die Index      | 300              |
| Material       | Aluminum         |
| Plating Type   | Tin - Hot Dipped |
| Trade Name     | HYREDUCER™       |
| UPC            | 781810192733     |

### Dimensions

|                                   |            |
|-----------------------------------|------------|
| Dimension - B Length fraction     | 2-7/10 in  |
| Dimension - B Length inch         | 2.70 in    |
| Dimension - Length Overall inch   | 6.00 in    |
| Dimension - Outside Diameter inch | 1.31 in    |
| Dimension - Strip Length inch     | 2-13/16 in |

### Conductor Related

|                               |           |
|-------------------------------|-----------|
| Conductor - AL Str Size A     | 500 kcmil |
| Conductor - AL Str Size B     | 350 kcmil |
| Conductor - Copper Str Size A | 500 kcmil |
| Conductor - Copper Str Size B | 350 kcmil |

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)