

YRB39U34TW

by Burndy
Catalog ID: YRB39U34TW

Prop 65 Notice

Hyreducer Splice; 750 kcmil 61 Str or 750 kcmil Compct (.908 Dia.) 61 Str (Barrel A); 500 kcmil 37 Str or 500 kcmil Compct 19 Str Al; 37 Str. Al&Cu (Barrel B)



Product Details

General

Color Code	Yellow
Connector Type	Reducer
Die Index	936
Material	Aluminum
Plating Type	Tin - Hot Dipped
Trade Name	HYREDUCER™
UPC	781810192764

Dimensions

Dimension - B Length fraction	2-87/100 in
Dimension - B Length inch	2.87 in
Dimension - Length Overall inch	6.74 in
Dimension - Outside Diameter inch	1.46 in
Dimension - Strip Length inch	3

Conductor Related

Conductor - AL Str Size A	750 kcmil
Conductor - AL Str Size B	500 kcmil
Conductor - Copper Str Size A	750 kcmil
Conductor - Copper Str Size B	500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)