

## YRB4039T

by Burndy  
Catalog ID: YRB4039T

Copper HYREDUCER™; 4.89 in L; 800 kcmil (Barrel A); 750 kcmil (Barrel B)



### Product Details

#### General

Color Code	Orange
Die Index	25
Material	Copper
Trade Name	HYREDUCER™
UPC	781810368022

#### Dimensions

Dimension - B Length inch	2.13 in
Dimension - Length BB inch	2.13 in
Dimension - Length Overall inch	4.89 in
Dimension - Outside Diameter inch	1.35 in

#### Conductor Related

Conductor - Copper Str Size A	800 kcmil
Conductor - Copper Str Size B	750 kcmil

#### Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

#### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)