

## YRB4434TTN

by Burndy  
Catalog ID: YRB4434TTN

Prop 65 Notice

Copper HYREDUCER™; 5.86 in L; Tin Plated; 1000 kcmil (1.152) (Barrel A);  
500 kcmil (.813) (Barrel B)



## Product Details

### General

Material	Copper
Plated	Y
Plating Type	Tin Plated
Trade Name	HYREDUCER™
UPC	781810439548

### Dimensions

Dimension - B Length inch	2.50 in
Dimension - Length BB inch	2.50 in
Dimension - Length Overall inch	5.86 in
Dimension - Outside Diameter inch	1.50 in

### Conductor Related

Conductor - Copper Str Size A	1000 kcmil
Conductor - Copper Str Size B	500 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)