

YRB4434TW

by Burndy
Catalog ID: YRB4434TW

Prop 65 Notice

Copper Hyreducer; 5.86 in L; Hot Tin Dipped; 1000 kcmil (1.152) (Barrel A); 500 kcmil (.813) (Barrel B)



Product Details

General

Material	Copper
Plating Type	Tin - Hot Dipped
Trade Name	HYREDUCER™
UPC	781810365199

Dimensions

Dimension - B Length inch	2.50 in
Dimension - Length BB inch	2.50 in
Dimension - Length Overall inch	5.86 in
Dimension - Outside Diameter inch	1.50 in

Conductor Related

Conductor - Copper Str Size A	1000 kcmil
Conductor - Copper Str Size B	500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)