

# YRB44U39G2

by Burndy  
Catalog ID: YRB44U39G2

Prop 65 Notice

UL Listed 90° C, 600 Volts to 35 KV.



## Product Details

### General

Connector Type	Reducer
Die Index	724
Material	Aluminum
Physical Attribute - Number of Holes	0
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYREDUCER™
UPC	781810215487
UPC 12 Digit	7818102154877

### Dimensions

Dimension - A Outside Diameter inch	1.62 in
Dimension - B Length fraction	2-1/4 in
Dimension - B Length inch	2.25 in
Dimension - B Outside Diameter inch	1.62 in
Dimension - L Length Overall mm	141 mm
Dimension - Length BB inch	2.25 in
Dimension - Length Overall inch	5.57 in
Dimension - Strip Length inch	2-5/16

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - AL Str Size A	1000
Conductor - AL Str Size A Range	1000
Conductor - AL Str Size B	750
Conductor - AL Str Size B Range	750
Conductor - Copper Str Size	1000

Conductor - Copper Str Size B	750
Conductor - Copper Str Size B Range	750

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	12
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)