

YRB6C6CTTN

by Burndy
Catalog ID: YRB6C6CTTN

Prop 65 Notice

Cu Splice, #6 Str(Cu)(Barrel A & B), 35 kV, 2.05" L, Tin Plating, Blue, 7 or 374 Index, For Cu to Cu



Product Details

General

Color Code	Blue
Die Index	7;374
Material	Copper
Plated	Y
Plating Type	Tin Plated
Trade Name	HYREDUCER™
UPC	781810238561

Dimensions

Dimension - B Length inch	0.90 in
Dimension - L Length Overall mm	52 mm
Dimension - Length BB inch	0.90 in
Dimension - Length Overall inch	2.05 in
Dimension - Outside Diameter inch	0.29 in

Conductor Related

Conductor - Copper Str Size A	6 AWG
Conductor - Copper Str Size B	6 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)