



YRV4CV6CL

by Burndy
Catalog ID: YRV4CV6CL

Cu Reducer Butt Splice, W/InspWindow, Barrel A:4 Barrel C:6 (Str), 1.24" L, Tin Plated, For Aircraft Applications.

Features: Cu Reducer Butt Splice, with Insp Window, 1.24 IN L, Tin Plated

Product Details

General

Application	For Splicing Two Different Size Wires, Aircraft Applications (Flexible Cables)
Connector Type	Reducer
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYREDUCER
Trade Name	HYREDUCER™
Type	Reducing Splices
UPC	781810085769

Dimensions

Dimension - A Outside Diameter inch	0.38 in
Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.61 in
Dimension - B Outside Diameter inch	0.3 in
Dimension - Length BB inch	0.52 in
Dimension - Length Overall inch	1.24 in
Length	1.24 in

Conductor Related

Conductor - Copper Flex H Size B Range	N/A
Conductor - Copper Str Size	4
Conductor - Copper Str Size B	6
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)