

YS1CLB

by Burndy
Catalog ID: YS1CLB

Prop 65 Notice

UNINSULATED BELLED COPPER COMPRESSION SPLICE, STANDARD LENGTH BELLED BARREL.



Product Details

General

Color Code	Green
Connector Type	Splice
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLINK™
UPC	781810506974
UPC 12 Digit	7818105069744

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.87 in
Dimension - L Length Overall mm	50 mm
Dimension - Length Overall inch	1.97 in
Dimension - Strip Length inch	15/16

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	2 (150/#24) DLO
Conductor - Copper Flex G Size	2 AWG
Conductor - Copper Flex H Size	2 AWG
Conductor - Copper Flex I Size	2 AWG
Conductor - Copper Flex K Size	2 AWG
Conductor - Copper Flex M Size	2 AWG
Conductor - Copper Str Compact Size	1 AWG
Conductor - Copper Str Navy Size	75 (37) Navy

Conductor - Copper Str Size	1 AWG
-----------------------------	-------

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)