

YS25UCG1

by Burndy
Catalog ID: YS25UCG1

URD Insulator Splice Kit, 1/0 AWG Comp, 1/0 Str Al, 1/0 AWG (6-1) ACSR, 1/0 Str Cu, 600 V



Product Details

General

Connector Type	Splice
Die Index	243;BG
Insulation	Y
Insulation Type	Diaform
Material	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810187753
UPC 12 Digit	7818101877533

Dimensions

Dimension - B Length inch	0.87 in
Dimension - Length Overall inch	2 in

Conductor Related

Conductor - ACSR Str Size A	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size A Range	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size B	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size B Range	1/0 (6/1) Raven AWG
Conductor - AL Str Size A	1/0 AWG
Conductor - AL Str Size A Range	1/0 AWG
Conductor - AL Str Size B	1/0 AWG
Conductor - AL Str Size B Range	1/0 AWG
Conductor - Copper Str Size A	1/0
Conductor - Copper Str Size A Range	1/0

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed

No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)