



## YS26FXLTCKITC

by Burndy  
Catalog ID: YS26FXLTCKITC

Prop 65 Notice

Electro-tin plated copper compression reducer/splice, with a through hole for cable inspection on each side, for 2/0 AWG wire.

## Product Details

### General

Color Code	Black
Color Code - Side A	Black
Color Code - Side B	Black
Connector Type	Splice;Reducer
Die Index	13
Die Index Run Side	13
Die Index Tap Side	13
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYSPLICE™
UPC	781810344125
UPC 12 Digit	7818103441255

### Dimensions

Dimension - B Length inch	1.10 in
Dimension - L Length Overall mm	66.5 mm
Dimension - Length BB inch	1.10 in
Dimension - Length Overall inch	2.62 in
Dimension - Strip Length inch	1.10

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Flex G Size A	2/0 AWG
----------------------------------	---------

Conductor - Copper Flex G Size B	2/0 AWG
Conductor - Copper Flex H Size A	2/0 AWG
Conductor - Copper Flex H Size B	2/0 AWG
Conductor - Copper Flex I Size A	2/0 AWG
Conductor - Copper Flex I Size B	2/0 AWG
Conductor - Copper Flex K Size A	2/0 AWG
Conductor - Copper Flex K Size B	2/0 AWG
Conductor - Copper Flex M Size A	2/0 AWG
Conductor - Copper Flex M Size B	2/0 AWG
Conductor - Copper Str Size	2/0 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)