

# YS26UCG1

by Burndy  
Catalog ID: YS26UCG1

URD Insulator Splice Kit, 2/0 AWG Comp, 2/0 Str Al, 2/0 AWG (6-1)  
ACSR, 2/0 Str Cu, 600 V



## Product Details

### General

Connector Type	Splice
Die Index	249;840
Insulation	Y
Insulation Type	Diaform
Material	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810187807
UPC 12 Digit	7818101878077

### Dimensions

Dimension - B Length inch	1.9 in
Dimension - Length Overall inch	4.12 in

### Conductor Related

Conductor - ACSR Str Size A	2/0 (6/1) Quail AWG
Conductor - ACSR Str Size A Range	2/0 (6/1) Quail AWG
Conductor - ACSR Str Size B	2/0 (6/1) Quail AWG
Conductor - ACSR Str Size B Range	2/0 (6/1) Quail AWG
Conductor - AL Str Size A	2/0 AWG
Conductor - AL Str Size A Range	2/0 AWG
Conductor - AL Str Size B	2/0 AWG
Conductor - AL Str Size B Range	2/0 AWG
Conductor - Copper Str Size A	2/0 AWG
Conductor - Copper Str Size A Range	2/0 AWG
Conductor - Copper Str Size B	2/0 AWG
Conductor - Copper Str Size B Range	2/0 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)