



YS27AT

by Burndy
Catalog ID: YS27AT

Prop 65 Notice

High Voltage Uninsulated Al Tube Compression Splice, 3/0 Str Al Cable, 4.69" L

Product Details

General

Color Code	Ruby
Connector Type	Splice
Die Index	467
Feature - Barrel Style	Tapered
Feature - Barrel Type	Standard
Material	Aluminum
Physical Attribute - Number of Crimps Required	3
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLINK™
UPC	781810001387

Dimensions

Dimension - B Length inch	2.04 in
Dimension - L Length Overall mm	119 mm
Dimension - Length Overall inch	4.69 in
Dimension - Outside Diameter inch	0.76 in
Dimension - Pad Width inch	2.27 in
Dimension - Strip Length inch	2 5/8

Conductor Related

Conductor - AL Str Size	3/0 AWG
-------------------------	---------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)